# EPF *i*protect<sup>®</sup> (Ecological Pressure Filter)

**High Pressure Filters** Max 700 I/min - 450 bar

# A compact, cost effective pressure filter solution

### **Designed with the** iprotect® patented filtration technology

The Parker EPF *i*protect® (Ecological High Pressure Filter) is designed to provide high quality filtration of hydraulic systems, providing new possibilities to reduce the cost of ownership by improving their productivity and profitability.

A radical, innovative approach was applied with the design of the EPF iprotect<sup>®</sup>, suitable for a flow capacity up to 700 l/min at 450 bar working pressure.

A new patented design of the filter element allows integration of the bypass valve and element core as re-usable parts in the filter bowl. This makes the product fool proof as there is no risk of forgetting to re-install re-usable parts.

With less space being available for filters, Parker has taken on board the requirement to provide more compact solutions. A unique feature is the filter element remains inside the filter bowl when changing the filter element. This can save over 500mm of space envelope in comparison with traditional high pressure filters.

- Unique OEM branding opportunities
- Easy to integrate into hydraulic manifold solutions





# Product Features:

The patented element design guarantees the quality of filtration, which directly impacts the oil cleanliness level as the usage of pirate type after market filters with unknown quality of filter media is excluded. This in-build safety has a direct, positive impact on the productivity and profitability of equipment.

- Guaranteed quality of filtration
- More compact solutions are possible •
- Filter element remains in filter bowl during filter service •
- Reduce waste of 50% •



•


Features	Advantages	Benefits
Patented filter element	Avoid use of non-genuine parts	Guaranteed quality of filtration
Filter element remains in filter bowl	Less space needed to	More compact solutions are possible
	change/service filter	Reduce service time for filter over 40%
Environmentally-friendly design	Reduces environmental waste over 50%	Lower disposal cost
Service-friendly product design	No handling of loose re-usable parts	No risk of making mistakes during change of element
Bypass valve integral part of filter bowl	Easy to integrate in manifold systems	More compact and lower cost of manifold (only one cavity is needed)
	Lower pressure lost across filter	Saving energy, improving system efficiency
Wide range of differential	Continuous feedback of condition	Optimizing filter element life
pressure indicators	filter elements	Contributes to scheduled maintenance


## **Typical Applications**

- Mobile working hydraulics
- Mobile drive system
- Pilot line filtration
- Servo controls
- Reverse flow valve applications
- Industrial working hydraulics
- Control systems

# The Parker EPF *i*protect<sup>®</sup> series patented bypass valve technology

Bypass settings are available up to 7 bar or completely blocked in conjunction with patented, high strength filter elements. The principle is based on differential pressure measurement across the filter element. During bypass only a part of the mainflow is flowing through the bypass valve.








Epf *i*protect<sup>®</sup> applies the latest generation of Microglass III filter media. The patented element design guarantees the quality of filtration.



**High Pressure Filters** 

## Selecting the right EPF element



## **EPF Spare Element Information**

#### Type QI

EPF Size1 L1 2 micron944418QEPF Size1 L1 5 micron944419QEPF Size1 L1 20 micron944420QEPF Size1 L1 20 micron944421QEPF Size 2 L1 2 micron944421QEPF Size 2 L1 5 micron944420QEPF Size 2 L1 5 micron944420QEPF Size 2 L1 10 micron944420QEPF Size 2 L1 20 micron944420QEPF Size 2 L2 2 micron944420QEPF Size 2 L2 2 micron944420QEPF Size 2 L2 2 micron944430QEPF Size 2 L2 20 micron944431QEPF Size 3 L1 2 micron944432QEPF Size 3 L1 2 micron944434QEPF Size 3 L1 2 micron944434QEPF Size 3 L1 2 micron944434QEPF Size 3 L2 2 micron944430QEPF Size 3 L2 2 micron944440QEPF Size 3 L2 10 micron944440QEPF Size 4 L1 2 micron944442QEPF Size 4 L2 2 micron944442QEPF Size 4 L
EPF Size1 L1 10 micron 9444200   EPF Size1 L1 20 micron 9444210   EPF Size 2 L1 2 micron 9444200   EPF Size 2 L1 5 micron 9444270   EPF Size 2 L1 10 micron 9444280   EPF Size 2 L1 20 micron 9444290   EPF Size 2 L1 20 micron 9444290   EPF Size 2 L2 2 micron 9444300   EPF Size 2 L2 2 micron 9444320   EPF Size 2 L2 10 micron 9444320   EPF Size 3 L1 2 micron 9444300   EPF Size 3 L2 2 micron 9444370   EPF Size 3 L2 2 micron 9444300   EPF Size 3 L2 2 micron 9444300   EPF Size 3 L2 10 micron 9444400   EPF Size 3 L2 10 micron 9444400   EPF Size 4 L1 2 micron 9444430   EPF Size 4 L1 2 micron 9444440   EPF Size 4 L1 2 micron 9444440   EPF Size 4 L1 2 micron 9444440   E
EPF Size1 L1 20 micron 9444210   EPF Size 2 L1 2 micron 9444200   EPF Size 2 L1 5 micron 9444270   EPF Size 2 L1 10 micron 9444280   EPF Size 2 L1 20 micron 9444290   EPF Size 2 L1 20 micron 9444300   EPF Size 2 L2 2 micron 9444300   EPF Size 2 L2 10 micron 9444300   EPF Size 2 L2 10 micron 9444300   EPF Size 2 L2 10 micron 9444300   EPF Size 3 L1 2 micron 9444300   EPF Size 3 L2 2 micron 9444300   EPF Size 3 L2 2 micron 9444300   EPF Size 3 L2 2 micron 9444430   EPF Size 3 L2 10 micron 9444400   EPF Size 3 L2 10 micron 9444400   EPF Size 4 L1 2 micron 9444400 <td< th=""></td<>
EPF Size 2 L1 2 micron 944426Q   EPF Size 2 L1 5 micron 944427Q   EPF Size 2 L1 10 micron 944428Q   EPF Size 2 L1 20 micron 944429Q   EPF Size 2 L2 2 micron 944430Q   EPF Size 2 L2 2 micron 944430Q   EPF Size 2 L2 2 micron 944430Q   EPF Size 2 L2 20 micron 944430Q   EPF Size 3 L1 0 micron 944430Q   EPF Size 3 L1 2 micron 944430Q   EPF Size 3 L2 2 micron 944440Q   EPF Size 3 L2 10 micron 944440Q   EPF Size 3 L2 10 micron 944444Q   EPF Size 4 L1 2 micron 944443Q   EPF Size 4 L1 2 micron 944444Q   EPF Size 4 L1 2 micron 944444Q   EPF Size 4 L1 2 micron 944445Q   EPF Size 4 L1 2 micron 944444Q   EP
EPF Size 2 L1 5 micron 9444270   EPF Size 2 L1 10 micron 9444280   EPF Size 2 L1 20 micron 9444290   EPF Size 2 L2 2 micron 9444300   EPF Size 2 L2 2 micron 9444310   EPF Size 2 L2 10 micron 9444320   EPF Size 2 L2 20 micron 9444310   EPF Size 3 L1 2 micron 9444320   EPF Size 3 L1 2 micron 9444340   EPF Size 3 L1 2 micron 9444370   EPF Size 3 L1 2 micron 9444370   EPF Size 3 L2 2 micron 9444380   EPF Size 3 L2 2 micron 9444370   EPF Size 3 L2 10 micron 9444370   EPF Size 3 L2 10 micron 9444430   EPF Size 3 L2 10 micron 9444430   EPF Size 3 L2 10 micron 9444400   EPF Size 4 L1 2 micron 9444400   EPF Size 4 L1 2 micron 9444430   EPF Size 4 L1 2 micron 9444430   EPF Size 4 L1 2 micron 9444440   EPF Size 4 L1 20 micron 9444450   EPF Size 4 L1 20 micron 9444450   EPF Size 4 L2 2 micron 9444450   <
EPF Size 2 L1 10 micron 9444280   EPF Size 2 L2 2 micron 9444290   EPF Size 2 L2 2 micron 9444300   EPF Size 2 L2 5 micron 9444310   EPF Size 2 L2 10 micron 9444320   EPF Size 2 L2 20 micron 9444320   EPF Size 3 L1 2 micron 9444320   EPF Size 3 L1 2 micron 9444320   EPF Size 3 L1 2 micron 9444340   EPF Size 3 L1 2 micron 9444360   EPF Size 3 L2 10 micron 9444380   EPF Size 3 L2 10 micron 9444390   EPF Size 3 L2 10 micron 944430   EPF Size 3 L2 10 micron 9444430   EPF Size 3 L2 10 micron 9444430   EPF Size 3 L2 10 micron 9444430   EPF Size 4 L1 2 micron 9444420   EPF Size 4 L1 2 micron 9444420   EPF Size 4 L1 2 micron 9444420   EPF Size 4 L1 2 micron 9444430   EPF Size 4 L1 20 micron 9444440   EPF Size 4 L1 20 micron 9444450   EPF Size 4 L2 2 micron 9444440   EPF Size 4 L2 2 micron 9444440   <
EPF Size 2 L1 20 micron 944429Q   EPF Size 2 L2 2 micron 944430Q   EPF Size 2 L2 5 micron 944431Q   EPF Size 2 L2 10 micron 944432Q   EPF Size 2 L2 20 micron 944433Q   EPF Size 3 L1 2 micron 944434Q   EPF Size 3 L1 2 micron 944436Q   EPF Size 3 L1 2 micron 944437Q   EPF Size 3 L2 2 micron 94443Q   EPF Size 3 L2 10 micron 944443Q   EPF Size 3 L2 10 micron 944443Q   EPF Size 3 L2 10 micron 944443Q   EPF Size 4 L1 2 micron 944444Q   EPF Size 4 L1 2 micron 944445Q   EPF Size 4 L2 2 micron 944445Q   EPF Size 4 L2 2 micron 944445Q   EPF Size 4 L2 10 micron 944444Q   EPF Size 4 L2 10 micron 944445Q
EPF Size 2 L2 2 micron 9444300   EPF Size 2 L2 5 micron 9444310   EPF Size 2 L2 10 micron 9444320   EPF Size 2 L2 20 micron 9444330   EPF Size 3 L1 2 micron 9444360   EPF Size 3 L1 2 micron 9444350   EPF Size 3 L1 5 micron 9444360   EPF Size 3 L1 20 micron 9444380   EPF Size 3 L2 2 micron 9444380   EPF Size 3 L2 2 micron 9444390   EPF Size 3 L2 10 micron 9444430   EPF Size 3 L2 10 micron 9444430   EPF Size 4 L1 2 micron 9444440   EPF Size 4 L1 20 micron 9444440   EPF Size 4 L1 20 micron 9444450   EPF Size 4 L2 2 micron 9444450   EPF Size 4 L2 2 micron 9444450   EPF Size 4 L2 10 micron 9444450   EPF Size 4 L2 10 micron 9444450
EPF Size 2 L2 5 micron 9444310   EPF Size 2 L2 10 micron 9444320   EPF Size 2 L2 20 micron 9444330   EPF Size 3 L1 2 micron 9444340   EPF Size 3 L1 5 micron 9444350   EPF Size 3 L1 5 micron 9444360   EPF Size 3 L1 20 micron 9444370   EPF Size 3 L2 2 micron 9444380   EPF Size 3 L2 2 micron 9444390   EPF Size 3 L2 2 micron 9444300   EPF Size 3 L2 10 micron 9444400   EPF Size 3 L2 10 micron 9444430   EPF Size 4 L1 2 micron 9444420   EPF Size 4 L1 2 micron 9444430   EPF Size 4 L1 2 micron 9444440   EPF Size 4 L1 2 micron 9444450   EPF Size 4 L1 2 micron 9444450   EPF Size 4 L1 2 micron 9444450   EPF Size 4 L2 2 micron 9444450   EPF Size 4 L2 2 micron 9444450   EPF Size 4 L2 10 micron 9444450   EPF Size 4 L2 10 micron 9444450   EPF Size 4 L2 10 micron 9444450
EPF Size 2 L2 10 micron 9444320   EPF Size 2 L2 20 micron 9444330   EPF Size 3 L1 2 micron 9444340   EPF Size 3 L1 5 micron 9444350   EPF Size 3 L1 10 micron 9444360   EPF Size 3 L1 20 micron 9444370   EPF Size 3 L2 2 micron 9444380   EPF Size 3 L2 2 micron 9444380   EPF Size 3 L2 5 micron 9444390   EPF Size 3 L2 0 micron 9444400   EPF Size 3 L2 0 micron 9444400   EPF Size 4 L1 2 micron 9444420   EPF Size 4 L1 5 micron 9444430   EPF Size 4 L1 2 micron 9444430   EPF Size 4 L1 2 micron 9444430   EPF Size 4 L1 2 micron 9444450   EPF Size 4 L1 2 micron 9444400   EPF Size 4 L2 2 micron 9444400   EPF Size 4 L2 5 micron 9444400   EPF Size 4 L2 5 micron 9444400   EPF
EPF Size 2 L2 20 micron 9444330   EPF Size 3 L1 2 micron 9444340   EPF Size 3 L1 5 micron 9444350   EPF Size 3 L1 10 micron 9444370   EPF Size 3 L1 20 micron 9444370   EPF Size 3 L2 2 micron 9444370   EPF Size 3 L2 2 micron 9444380   EPF Size 3 L2 2 micron 9444370   EPF Size 3 L2 10 micron 9444430   EPF Size 3 L2 20 micron 9444400   EPF Size 4 L1 2 micron 9444420   EPF Size 4 L1 2 micron 9444430   EPF Size 4 L1 2 micron 9444430   EPF Size 4 L1 2 micron 9444440   EPF Size 4 L1 20 micron 9444450   EPF Size 4 L2 2 micron 9444450   EPF Size 4 L2 2 micron 9444450   EPF Size 4 L2 2 micron 9444470   EPF Size 4 L2 5 micron 9444470
EPF Size 3 L1 2 micron 944434Q   EPF Size 3 L1 5 micron 944435Q   EPF Size 3 L1 10 micron 944436Q   EPF Size 3 L1 20 micron 944437Q   EPF Size 3 L2 2 micron 944438Q   EPF Size 3 L2 2 micron 944438Q   EPF Size 3 L2 2 micron 944430Q   EPF Size 3 L2 10 micron 944440Q   EPF Size 3 L2 20 micron 944441Q   EPF Size 4 L1 2 micron 944443Q   EPF Size 4 L1 2 micron 944444Q   EPF Size 4 L1 20 micron 944444Q   EPF Size 4 L2 2 micron 944444Q   EPF Size 4 L2 2 micron 94444Q   EPF Size 4 L2 2 micron 94444Q   EPF Size 4 L2 0 micron 94444Q   EPF Size 4 L2 0 micron 94444Q   EPF Size 4 L2 10 micron 94444Q
EPF Size 3 L1 5 micron 9444350   EPF Size 3 L1 10 micron 9444360   EPF Size 3 L1 20 micron 9444370   EPF Size 3 L2 2 micron 9444380   EPF Size 3 L2 5 micron 9444390   EPF Size 3 L2 10 micron 9444400   EPF Size 3 L2 20 micron 9444410   EPF Size 4 L1 2 micron 9444420   EPF Size 4 L1 2 micron 9444430   EPF Size 4 L1 10 micron 9444450   EPF Size 4 L1 20 micron 9444450   EPF Size 4 L1 2 micron 9444450   EPF Size 4 L2 5 micron 9444450
EPF Size 3 L1 10 micron 944436Q   EPF Size 3 L2 20 micron 944437Q   EPF Size 3 L2 20 micron 944438Q   EPF Size 3 L2 50 micron 944439Q   EPF Size 3 L2 10 micron 944440Q   EPF Size 3 L2 20 micron 944440Q   EPF Size 3 L2 20 micron 944440Q   EPF Size 4 L1 20 micron 944442Q   EPF Size 4 L1 5 micron 944443Q   EPF Size 4 L1 5 micron 944443Q   EPF Size 4 L1 20 micron 944445Q   EPF Size 4 L2 10 micron 944445Q   EPF Size 4 L2 10 micron 944445Q
EPF Size 3 L1 20 micron 944437Q   EPF Size 3 L2 2 micron 944438Q   EPF Size 3 L2 5 micron 944439Q   EPF Size 3 L2 10 micron 944440Q   EPF Size 3 L2 20 micron 9444410   EPF Size 4 L1 2 micron 944442Q   EPF Size 4 L1 5 micron 944443Q   EPF Size 4 L1 5 micron 944443Q   EPF Size 4 L1 0 micron 944444Q   EPF Size 4 L1 20 micron 944445Q   EPF Size 4 L2 2 micron 944445Q   EPF Size 4 L2 5 micron 94444Q   EPF Size 4 L2 5 micron 944445Q
EPF Size 3 L2 2 micron 9444380   EPF Size 3 L2 5 micron 9444390   EPF Size 3 L2 10 micron 9444400   EPF Size 3 L2 20 micron 9444410   EPF Size 4 L1 2 micron 9444420   EPF Size 4 L1 5 micron 9444430   EPF Size 4 L1 5 micron 9444440   EPF Size 4 L1 20 micron 9444440   EPF Size 4 L1 20 micron 9444450   EPF Size 4 L2 2 micron 9444450   EPF Size 4 L2 5 micron 9444470   EPF Size 4 L2 10 micron 9444480
EPF Size 3 L2 5 micron 944439Q   EPF Size 3 L2 10 micron 944440Q   EPF Size 3 L2 20 micron 944441Q   EPF Size 4 L1 2 micron 944442Q   EPF Size 4 L1 5 micron 944443Q   EPF Size 4 L1 10 micron 944443Q   EPF Size 4 L1 10 micron 944445Q   EPF Size 4 L2 2 micron 944445Q   EPF Size 4 L2 5 micron 944445Q   EPF Size 4 L2 5 micron 944445Q   EPF Size 4 L2 10 micron 944445Q
EPF Size 3 L2 10 micron 9444400   EPF Size 3 L2 20 micron 9444410   EPF Size 4 L1 2 micron 9444420   EPF Size 4 L1 5 micron 9444430   EPF Size 4 L1 10 micron 9444440   EPF Size 4 L1 20 micron 9444440   EPF Size 4 L2 20 micron 94444450   EPF Size 4 L2 2 micron 9444460   EPF Size 4 L2 5 micron 9444470   EPF Size 4 L2 10 micron 9444480
EPF Size 3 L2 20 micron 9444410   EPF Size 4 L1 2 micron 9444420   EPF Size 4 L1 5 micron 9444430   EPF Size 4 L1 10 micron 9444440   EPF Size 4 L1 20 micron 9444450   EPF Size 4 L2 2 micron 9444400   EPF Size 4 L2 5 micron 9444470   EPF Size 4 L2 10 micron 9444480
EPF Size 4 L1 2 micron 9444420   EPF Size 4 L1 5 micron 9444430   EPF Size 4 L1 10 micron 9444440   EPF Size 4 L1 20 micron 9444450   EPF Size 4 L2 2 micron 9444400   EPF Size 4 L2 5 micron 9444470   EPF Size 4 L2 10 micron 9444480
EPF Size 4 L1 5 micron 9444430   EPF Size 4 L1 10 micron 9444440   EPF Size 4 L1 20 micron 9444450   EPF Size 4 L2 2 micron 9444460   EPF Size 4 L2 5 micron 9444470   EPF Size 4 L2 10 micron 9444480
EPF Size 4 L1 10 micron 944444Q   EPF Size 4 L1 20 micron 944445Q   EPF Size 4 L2 2 micron 944446Q   EPF Size 4 L2 5 micron 944447Q   EPF Size 4 L2 10 micron 944448Q
EPF Size 4 L1 20 micron 9444450   EPF Size 4 L2 2 micron 9444460   EPF Size 4 L2 5 micron 9444470   EPF Size 4 L2 10 micron 9444480
EPF Size 4 L2 2 micron 944446Q   EPF Size 4 L2 5 micron 944447Q   EPF Size 4 L2 10 micron 944448Q
EPF Size 4 L2 5 micron 944447Q   EPF Size 4 L2 10 micron 944448Q
EPF Size 4 L2 10 micron 944448Q
EPF Size 4 L2 20 micron 944449Q
EPF Size 5 L1 2 micron 944450Q
EPF Size 5 L1 5 micron 944451Q
EPF Size 5 L1 10 micron 944452Q
EPF Size 5 L1 20 micron 944453Q

#### **Type QIH**

EPF High Strength Size1 L1 2 micron	944481Q
EPF High Strength Size1 L1 5 micron	944482Q
EPF High Strength Size1 L1 10 micron	944483Q
EPF High Strength Size1 L1 20 micron	944484Q
EPF High Strength Size 2 L1 2 micron	944489Q
EPF High Strength Size 2 L1 5 micron	944490Q
EPF High Strength Size 2 L1 10 micron	944491Q
EPF High Strength Size 2 L1 20 micron	944492Q
EPF High Strength Size 2 L2 2 micron	944493Q
EPF High Strength Size 2 L2 5 micron	944494Q
EPF High Strength Size 2 L2 10 micron	944495Q
EPF High Strength Size 2 L2 20 micron	944496Q
EPF High Strength Size 3 L1 2 micron	944497Q
EPF High Strength Size 3 L1 5 micron	944498Q
EPF High Strength Size 3 L1 10 micron	944499Q
EPF High Strength Size 3 L1 20 micron	944500Q
EPF High Strength Size 3 L2 2 micron	944501Q
EPF High Strength Size 3 L2 5 micron	944502Q
EPF High Strength Size 3 L2 10 micron	944503Q
EPF High Strength Size 3 L2 20 micron	944504Q
EPF High Strength Size 4 L1 2 micron	944505Q
EPF High Strength Size 4 L1 5 micron	944506Q
EPF High Strength Size 4 L1 10 micron	944507Q
EPF High Strength Size 4 L1 20 micron	944508Q
EPF High Strength Size 4 L2 2 micron	944509Q
EPF High Strength Size 4 L2 5 micron	944510Q
EPF High Strength Size 4 L2 10 micron	944511Q
EPF High Strength Size 4 L2 20 micron	944512Q
EPF High Strength Size 5 L1 2 micron	944513Q
EPF High Strength Size 5 L1 5 micron	944514Q
EPF High Strength Size 5 L1 10 micron	944515Q
EPF High Strength Size 5 L1 20 micron	944516Q

### Type QIR

EPF Size1 L1 2 micron reverse flow	944561Q
EPF Size1 L1 5 micron reverse flow	944562Q
EPF Size1 L1 10 micron reverse flow	944563Q
EPF Size1 L1 20 micron reverse flow	944564Q
EPF Size 2 L1 2 micron reverse flow	944569Q
EPF Size 2 L1 5 micron reverse flow	944570Q
EPF Size 2 L1 10 micron reverse flow	944571Q
EPF Size 2 L1 20 micron reverse flow	944572Q
EPF Size 2 L2 2 micron reverse flow	944573Q
EPF Size 2 L2 5 micron reverse flow	944574Q
EPF Size 2 L2 10 micron reverse flow	944575Q
EPF Size 2 L2 20 micron reverse flow	944576Q
EPF Size 3 L1 2 micron reverse flow	944577Q
EPF Size 3 L1 5 micron reverse flow	944578Q
EPF Size 3 L1 10 micron reverse flow	944579Q
EPF Size 3 L1 20 micron reverse flow	944580Q
EPF Size 3 L2 2 micron reverse flow	944581Q
EPF Size 3 L2 5 micron reverse flow	944582Q
EPF Size 3 L2 10 micron reverse flow	944583Q
EPF Size 3 L2 20 micron reverse flow	944584Q
EPF Size 4 L1 2 micron reverse flow	944585Q
EPF Size 4 L1 5 micron reverse flow	944586Q
EPF Size 4 L1 10 micron reverse flow	944587Q
EPF Size 4 L1 20 micron reverse flow	944588Q
EPF Size 4 L2 2 micron reverse flow	944589Q
EPF Size 4 L2 5 micron reverse flow	944590Q
EPF Size 4 L2 10 micron reverse flow	944591Q
EPF Size 4 L2 20 micron reverse flow	944592Q
EPF Size 5 L1 2 micron reverse flow	944593Q
EPF Size 5 L1 5 micron reverse flow	944594Q
EPF Size 5 L1 10 micron reverse flow	944595Q
EPF Size 5 L1 20 micron reverse flow	944596Q



# Protecting your system and the environment

# Protect your system performance and profit

The new *i*protect<sup>®</sup> generation of filter elements provide high filtration performance combined with Parker technology. The bespoke design prevents the use of pirate type alternatives.

#### Less space needed to accommodate the filter

More compact solutions are possible as the filter element remains in the filter bowl during change of filter element. Compared to traditional solutions it does not only save space, it also reduces the required manual handling during the filter change process.

# Saving cost and our environment

What does it take to introduce a new groundbreaking design which saves the environment? Parker's EPF *i*protect® applies a re-usable element core and

applies a re-usable element core and bypass, both integral parts of the filter bowl. This solution avoids the handling of re-usable parts during element change and reduces over

# Smart valve technology

50% disposal weight.

Parker hydraulic control valve technology is applied for the reusable bypass valve. This leakagefree valve



has a patented interface with the filter element, which ensures that genuine parts are always applied. With bypass settings up to 7 bar filtration during cold start conditions, more compact solutions, can be realised. The valve also optimizes the flow path, reducing the pressure lost across the filter.

#### Easier to integrate

Parker has set the trend to integrate filtration into manifolds. With Parker's EPF *i*protect<sup>®</sup> we have taken the design one step further. Only one cavity is



needed to accomodate the filter instead of two, this is because the re-usable bypass valve is integrated into the filter bowl, reducing space and cost.

# Customized solutions

Parker's motion & control technologies provide new opportunities for our customers. Customized manifolds or duplex



filters, as in this example offer complete automatic change-over. The EPF *i*protect<sup>®</sup> contributes to realizing new solutions, improving your productivity and profitability.

#### A protective 'gene'

The performance and profitability of systems directly depends upon the filter media.



It goes without saying that Parker's products aim to avoid the use of unknown filter performance, jeopardizing safety and performance. Our Microglass III media is continuously upgraded and acts as a protective 'gene' in the system.


# When going into reverse

Parker's EPF can be equipped with an optional reverse flow. This valve assembly is integrated in the



element end cap and isolates the filter medium during reverse flow conditions.

138



allows integration of the bypass valve and element core as re-usable parts in the filter bowl. This results in cost reduction when integrating the high pressure filter in manifold type solutions. But it also reduces the waste when changing the filter element by over 50% as the element core is an integral part of the filter bowl.

A new design of the filter element

The design of the EPF *i*protect<sup>®</sup>, is unique, there is no need to re-install any re-usable parts as with some other filters in the market. This makes the product fool proof as there is no risk of forgetting to re-install re-usable parts.



#### Replacing the filter element:

- Drain the filter housing using the plugged drain port.
- Thanks to the filter lock the element remains in the bowl.
- Pull out the old element. The re-usable element core and bypass valve are integral parts of the bowl.
- Filtration is from 'Out to In,' the element core is located in the clean oil side.
- Just drop the new element in the bowl.
- Screw the bowl, including element into the filter head.





Size 1

## Specification EPF *i*protect<sup>®</sup> Size 1

#### Specification

Nominal flow 40 l/min

#### Pressure ratings

Maximum allowable operationg pressure 450 bar Filter housing pressure pulse fatigue tested 10^6 pulses 0-414 bar

#### Connections Inlet and outlet connections are threaded internally

Connection style Thread G<sup>1</sup>/<sub>2</sub> Threat SAE 8

Filter housing

Head material cast iron (GSI) Bowl material steel

#### Seal material

Nitrile of Fluorelastomer

#### Operating temperature range

Seal material Nitrile : -40 °C to +100 °C Seal material Fluorelastomer : -20 °C to +120 °C

# Bypass valve & Indicator settingsBypassIndicator3.5 bar2.5 bar5.0 bar3.5 bar7.0 bar5.0 barBlocked5.0 bar

#### Filter element Degree of filtration Determined by multipass test in accordance to ISO16889

#### Flow fatigue characteristics

Filter media is supported so that the optimal fatigue life is achieved (ISO 3724)

#### Microglass III

Supported with epoxy coated metal wire mesh, end cap material reinforced composite and reusable metal inner core. Collapse pressure 25 bar (ISO 2941)

#### High collapse elements

To be used when bypass blocked option is selected Collapse pressure 210 bar (ISO 2941)

#### Indicator options

Indicating differential pressure: 2.5 +/- 0.3 bar 3.5 +/- 0.3 bar 5.0 +/- 0.3 bar


Visual M3 Electrical T1 Electronic F1 (PNP) Electronic F2 (NPN) Atex versions are available on request

#### Weights (kg)

EPF Size 1: 3

#### Fluid compatibility

- Hydraulic mineral oils H to class HLPD (DIN51524)
- · Operating fluids DIN ISO 2943
- Lubrication fluids ISO6743, APJ, DIN 51517, ACEA, ASTM
- Vegetable oils
- 60/40 Water Glycols
- · On request Industrial grade phosphate esters
- · Non aggressive synthetic oils
- · Non aggressive bio-degradable oils
- (HETG, HEPG and HEES to VDMA 24568)




#### EPF iprotect® - Size 1 (Inline)


## EPF iprotect® Size 1 Pressure Drop Curves


With 3.5 bar bypass the recommended initial pressure drop max is 1.2 bar

With 7.0 bar bypass the recommended initial pressure drop max is 2.3 bar

If the medium used has a viscosity different from 30cSt. pressure drop over the filter can be estimated as follows: The total  $\Delta p$  = housing  $\Delta ph$  + (element  $\Delta pe \times working viscosity/30).$ 









02QIH

-05QIH

-10QIH

20QIH

40

Size 2

## Specification EPF *i*protect<sup>®</sup> Size 2

Specification

Nominal flow >100 l/min

Pressure ratings Maximum allowable operationg pressure 450 bar Filter housing pressure pulse fatigue tested 10^6 pulses 0-414 bar

Connections Inlet and outlet connections are threaded internally

Connection style Thread  $G^{3/4}$ Thread SAE 12 Thread M27, ISO 6149 SAE flange  $\frac{3}{4} = 6000M$ 

SAE flange ¾ = 6000 Manifold Filter housing

Head material cast iron (GSI) Bowl material steel

Seal material Nitrile of Fluorelastomer

Operating temperature range Seal material Nitrile : -40 °C to +100 C Seal material Fluorelastomer : -20 °C to +120 C Bypass valve & Indicator settingsBypassIndicator3.5 bar2.5 bar5.0 bar3.5 bar7.0 bar5.0 barBlocked5.0 bar

#### Filter element

Degree of filtration Determined by multipass test in accordance to ISO16889

#### Flow fatigue characteristics

Filter media is supported so that the optimal fatigue life is achieved (ISO 3724)

#### Microglass III

Supported with epoxy coated metal wire mesh, end cap material reinforced composite and reusable metal inner core. Collapse pressure 25 bar (ISO 2941)

#### High collapse elements

To be used when bypass blocked option is selected

Collapse pressure 210 bar (ISO 2941)

#### Indicator options

Indicating differential pressure: 2.5 +/- 0.3 bar 3.5 +/- 0.3 bar 5.0 +/- 0.3 bar Visual M3 Electrical T1

Electronic F1 (PNP) Electronic F2 (NPN)

Atex versions are available on request


Weights (kg)

EPF Size 2 length 1: 4,2 EPF Size 2 length 2: 5,7

#### Fluid compatibility

 Hydraulic mineral oils H to class HLPD (DIN51524)

- · Operating fluids DIN ISO 2943
- Lubrication fluids ISO6743, APJ, DIN 51517, ACEA, ASTM
- · Vegetable oils
- · 60/40 Water Glycols
- · On request Industrial grade phosphate esters
- Non aggressive synthetic oils
- Non aggressive bio-degradable oils (HETG, HEPG and HEES to VDMA 24568)






Parker Hannifin Hydraulic Filter Division Europe FDHB500UK/EPF

### EPF iprotect® Size 2 Pressure Drop Curves


With 3.5 bar bypass the recommended initial pressure drop max is 1.2 bar

With 7.0 bar bypass the recommended initial pressure drop max is 2.3 bar


If the medium used has a viscosity different from 30cSt. pressure drop over the filter can be estimated as follows: The total  $\Delta p$  = housing  $\Delta ph$  + (element  $\Delta pe x$  working viscosity/30).










#### EPF Size 2 Length 1 Filter Elements with reverse flow valve





#### EPF Size 2 Length 1 High Strength Filter Elements












#### **EPF Size 2 Length 2 High Strength Filter Elements**



Size 3

## Specification EPF *i*protect<sup>®</sup> Size 3

Specification

Nominal flow >160 l/min

Pressure ratings Maximum allowable operationg pressure 450 bar Filter housing pressure pulse fatigue tested 10^6 pulses 0-414 bar

Connections Inlet and outlet connections are threaded internally

Connection style Thread G1 Thread SAE 16 Thread M33, ISO 6149 SAE flange 1 = 6000M SAE flange 1 = 6000

Filter housing Head material cast iron (GSI) Bowl material steel

Seal material Nitrile of Fluorelastomer

Operating temperature range Seal material Nitrile : -40 °C to +100 °C Seal material Fluorelastomer : -20 °C to +120 °C Bypass valve & Indicator settingsBypassIndicator3.5 bar2.5 bar5.0 bar3.5 bar7.0 bar5.0 barBlocked5.0 bar

#### Filter element Degree of filtration

Determined by multipass test in accordance to ISO16889

#### Flow fatigue characteristics

Filter media is supported so that the optimal fatigue life is achieved (ISO 3724)

#### Microglass III

Supported with epoxy coated metal wire mesh, end cap material reinforced composite and reusable metal inner core. Collapse pressure 25 bar (ISO 2941)

#### High collapse elements

To be used when bypass blocked option is selected

Collapse pressure 210 bar (ISO 2941)

#### Indicator options

Indicating differential pressure: 2.5 +/- 0.3 bar 3.5 +/- 0.3 bar 5.0 +/- 0.3 bar Visual M3

Electrical T1 Electronic F1 (PNP) Electronic F2 (NPN) Atex versions are available on request

#### Weights (kg)


EPF Size 3 length 1: 6,7 EPF Size 3 length 2: 9,2

#### Fluid compatibility

Hydraulic mineral oils H to class HLPD (DIN51524)

- · Operating fluids DIN ISO 2943
- Lubrication fluids ISO6743, APJ, DIN 51517, ACEA, ASTM
- · Vegetable oils
- · 60/40 Water Glycols
- · On request Industrial grade phosphate esters
- · Non aggressive synthetic oils
- Non aggressive bio-degradable oils
- (HETG, HEPG and HEES to VDMA 24568)

#### EPF iprotect® - Size 3 (Inline)




Parker Hannifin Hydraulic Filter Division Europe FDHB500UK/EPF


### EPF iprotect® Size 3 Pressure Drop Curves

With 3.5 bar bypass the recommended initial pressure drop max is 1.2 bar


With 7.0 bar bypass the recommended initial pressure drop max is 2.3 bar


If the medium used has a viscosity different from 30cSt. pressure drop over the filter can be estimated as follows: The total  $\Delta p$  = housing  $\Delta ph$  + (element  $\Delta pe x$  working viscosity/30).






EFP Size 3 Length 1 Filter Elements with reverse flow valve








Flow (I/min)

EPF Size 3 Length 2 Filter Elements











Size 4

### Specification EPF iprotect® Size 4

Specification

Nominal flow >320 l/min

Pressure ratings Maximum allowable operationg pressure 450 bar Filter housing pressure pulse fatigue tested 10^6 pulses 0-414 bar

Connections Inlet and outlet connections are threaded internally

Connection style Thread G11/4 Thread G11/2 Thread SAE 20 Thread SAE 24 Thread M42, ISO 6149 SAE flange 1¼ = 6000M SAE flange 1¼ = 6000

Manifold Filter housing

Head material cast iron (GSI) Bowl material steel

Seal material Nitrile of Fluorelastomer

#### Operating temperature range

Seal material Nitrile : -40 °C to +100 °C Seal material Fluorelastomer : -20 °C to +120 °C Bypass valve & Indicator settingsBypassIndicator3.5 bar2.5 bar5.0 bar3.5 bar7.0 bar5.0 barBlocked7.0 bar

#### Filter element

Degree of filtration Determined by multipass test in accordance to ISO16889

#### Flow fatigue characteristics

Filter media is supported so that the optimal fatigue life is achieved (ISO 3724)

#### Microglass III

Supported with epoxy coated metal wire mesh, end cap material reinforced composite and reusable metal inner core. Collapse pressure 25 bar (ISO 2941)

#### High collapse elements

To be used when bypass blocked option is selected

Collapse pressure 210 bar (ISO 2941)

#### Indicator options

Indicating differential pressure: 2.5 +/- 0.3 bar 3.5 +/- 0.3 bar 5.0 +/- 0.3 bar Visual M3

Electrical T1 Electronic F1 (PNP) Electronic F2 (NPN)

#### Atex versions are available on request


Weights (kg)

EPF Size 4 length 1: 15,8 EPF Size 4 length 2: 20,3

#### Fluid compatibility


 Hydraulic mineral oils H to class HLPD (DIN51524)

- · Operating fluids DIN ISO 2943
- Lubrication fluids ISO6743, APJ, DIN 51517, ACEA, ASTM
- · Vegetable oils
- · 60/40 Water Glycols
- · On request Industrial grade phosphate esters
- Non aggressive synthetic oils
- Non aggressive bio-degradable oils (HETG, HEPG and HEES to VDMA 24568)



162 Hex 24 mm, Torque 45 km, Vent plus (SE-4) Hex 15 mm, Torque 35-40 km,

EPF iprotect® - Size 4 (Manifold)



Parker Hannifin Hydraulic Filter Division Europe FDHB500UK/EPF





## EPF iprotect® Size 4 Pressure Drop Curves

With 3.5 bar bypass the recommended initial pressure drop max is 1.2 bar


With 7.0 bar bypass the recommended initial pressure drop max is 2.3 bar


If the medium used has a viscosity different from 30cSt. pressure drop over the filter can be estimated as follows: The total  $\Delta p$  = housing  $\Delta ph$  + (element  $\Delta pe x$  working viscosity/30).








EPF Size 4 Length 1 Filter Elements with reverse flow valve















#### EPF Size 4 Length 2 High Strength Filter Elements



Size 5

## Specification EPF *i*protect<sup>®</sup> Size 5

Specification

Nominal flow >320 l/min

Pressure ratings Maximum allowable operationg pressure 450 bar Filter housing pressure pulse fatigue tested 10^6 pulses 0-414 bar

Connections Inlet and outlet connections are threaded internally

Connection style Thread G1½ Thread SAE 24 Manifold SAE flange 1½ - 6000M Filter housing Head material cast iron (GSI) Bowl material steel Seal material

#### Nitrile of Fluorelastomer

Operating temperature range Seal material Nitrile : -40 °C to +100 °C Seal material Fluorelastomer : -20 °C to +120 °C Bypass valve & Indicator settingsBypassIndicator3.5 bar2.5 bar5.0 bar3.5 bar7.0 bar5.0 barBlocked5.0 bar

#### Filter element

Degree of filtration Determined by multipass test in accordance to ISO16889

#### 5010009

Flow fatigue characteristics Filter media is supported so that the optimal fatigue life is achieved (ISO 3724)

#### Microglass III

Supported with epoxy coated metal wire mesh, end cap material reinforced composite and reusable metal inner core. Collapse pressure 25 bar (ISO 2941)

#### High collapse elements

To be used when bypass blocked option is selected

Collapse pressure 210 bar (ISO 2941)

#### Indicator options

Indicating differential pressure: 2.5 +/- 0.3 bar 3.5 +/- 0.3 bar 5.0 +/- 0.3 bar Visual M3 Electrical T1


Electronic F1 (PNP)


Electronic F2 (NPN) Atex versions are available on request

### Weights (kg)

EPF Size 5 length 1: 31

- Fluid compatibility
- Hydraulic mineral oils H to class HLPD (DIN51524)
- Operating fluids DIN ISO 2943
- Lubrication fluids ISO6743, APJ, DIN 51517, ACEA, ASTM
- · Vegetable oils
- · 60/40 Water Glycols
- · On request Industrial grade phosphate esters
- Non aggressive synthetic oils
- Non aggressive bio-degradable oils (HETG, HEPG and HEES to VDMA 24568)







Parker Hannifin Hydraulic Filter Division Europe FDHB500UK/EPF


## EPF iprotect<sup>®</sup> - Size (Manifold)


## EPF iprotect<sup>®</sup> Size 5 Pressure Drop Curves


With 3.5 bar bypass the recommended initial pressure drop max is 1.2 bar


With 7.0 bar bypass the recommended initial pressure drop max is 2.3 bar


If the medium used has a viscosity different from 30cSt. pressure drop over the filter can be estimated as follows: The total  $\Delta p$  = housing  $\Delta ph$  + (element  $\Delta pe x$  working viscosity/30).















### Parts list

Index	Description	Part number
1	Indicator	On Request
2	Plug	On Request
3	Filter head	On Request
4	Filter element	See element table
5	Back-up ring	In seal kit/spare filter elements
6	O-ring	In seal kit/ spare filter elements
7	Filter bowl	On Request
8	Drain plug	On Request

## Seal kit numbers

Filter	Nitrile	Fluorelastomer
EPF 1	EPFSK001	EPFSK011
EPF 2	EPFSK002	EPFSK012
EPF 3	EPFSK003	EPFSK013
EPF 4 + 5	EPFSK004	EPFSK014





# **Indicator Options**

# FMU Ap-Indicators and Pressure Indicators

FMUT Electrical

**Contact configuration** 

Electrical Indicator Type T1

P1-P2

Rated	Non-i	nductiv	ve load	(A)	Induct	Inductive load (A)				+ (A)	
voltage	Resisti	ve load	Lamp le	oad	Inductive load		Motor I	oad	current (A)		
	N.C.	N.O.	N.C.	N.O.	N.C.	N.O.	N.C.	N.O.	N.C.	N.O.	
125VAC	ł	5	1.5	0.7	;	3	2.5	1.3			
250VAC	;	3	1.0	0.5	2	2	1.5	0.8	00	10	
8VDC	ł	5	2	2	5	4	3	3	20 max.	max.	
14VDC	ł	5	2	2	4	4	3	3			
30VDC		4	2	2	3	3	3	3			
125VDC	0	.4	0.	05	0.4	0.4	0.0	)5			
250VDC	0	.2	0.	03	0.2	0.2	0.0	03			


Rotating part 360°

Low pressure

High pressure

Enclosure classIP65Electrical connectorDIN 43650Overvoltage categoryII (EN61010-1)

FMUM3 Visual Auto Reset Operation



**FMUF Electronic** 


COM

Ó

Contact configuration

(2)

Indication (N.O)





No

Vormally closed (N.C)

3

connect





SAE 8

High pressure

SAE8

#### Thermal lock-out (standard setting +20 °C)

· Indicator operates only when temperature is above setting.

Ind. press.		LED s	tatus		Output
setting	G	Y1	Y2	R	
< 50 %	$\otimes$				-
50 %	$\otimes$	$\otimes$			-
75 %	$\otimes$	$\otimes$	$\otimes$	[	2 active
100 %	$\otimes$	$\otimes$	$\otimes$	8	1 active

Enclosure class	IP65
Electrical connector	DIN 43650, cable connection PG9 or optinally M12 4-pin
Input supply voltage	+10 to 36 Vdc
*Indication output	max. 300 mA/36 Vdc
Output type:	N.O. or N.C./NPN or PNP

Note: Do not connect output terminals 1 or 2 directly (without load) to power supply terminals, because this will damage the equipment.

# Filter media efficiency

		Degree o	f filtration					
Av	erage filtration	n beta ratio ß (l	SO 16889) / pa	rticle size µm	[c]		Code	
ßx(c)=2	ßx(c)=10	ßx(c)=75	ßx(c)=100	ßx(c)=200	ßx(c)=1000			
	% efficie	ency, based on t	he above beta ra	tion (ßx)		Disposable	Element	High strength
50.0%	90.0%	98.7%	99.0%	99.5%	99.9%	Microglass III	with reverse flow valve	Element
N/A	N/A	N/A	N/A	N/A	4.5	02QI	02QIR	02QIH
N/A	N/A	4.5	5	6	7	05QI	05QIR	05QIH
N/A	6	8.5	9	10	12	10QI	10QIR	10QIH
6	11	17	18	20	22	20QI	20QIR	20QIH

# Ordering information. Standard part numbers

Filter Assemblies	Part Number	Flow (l/min)	Model Number	Element length	Media Rating (micron)	Seals	Indicator	Bypass (bar)	Ports	Replacement elements
	EPF1105QIBPMG081	40	EFP1	1	5	Nitrile	Plugged port	7	G1/2"	944419Q
	EPF1110QIBPMG081	40	EFP1	1	10	Nitrile	Plugged port	7	G1/2"	944420Q
	EPF1120QIBPMG081	40	EFP1	1	20	Nitrile	Plugged port	7	G1/2"	944421Q
	EPF2205QIBPMG121	140	EPF2	2	5	Nitrile	Plugged port	7	G3/4"	944431Q
	EPF2210QIBPMG121	140	EPF2	2	10	Nitrile	Plugged port	7	G3/4"	944432Q
	EPF2220QIBPMG121	140	EPF2	2	20	Nitrile	Plugged port	7	G3/4"	944433Q
	EPF3205QIBPMG161	250	EPF3	2	5	Nitrile	Plugged port	7	G1"	944439Q
	EPF3210QIBPMG161	250	EPF3	2	10	Nitrile	Plugged port	7	G1"	944440Q
	EPF3220QIBPMG161	250	EPF3	2	20	Nitrile	Plugged port	7	G1"	944441Q
	EPF4205QIBPMG201	450	EPF4	2	5	Nitrile	Plugged port	7	G11/4"	944447Q
	EPF4210QIBPMG201	450	EPF4	2	10	Nitrile	Plugged port	7	G11/4"	944448Q
	EPF4220QIBPMG201	450	EPF4	2	20	Nitrile	Plugged port	7	G11/4"	944449Q
	EPF5105QIBPMG241	500	EPF5	1	5	Nitrile	Plugged port	7	G11/2"	944451Q
	EPF5110QIBPMG241	500	EPF5	1	10	Nitrile	Plugged port	7	G11/2"	944452Q
	EPF5120QIBPMG241	500	EPF5	1	20	Nitrile	Plugged port	7	G11/2"	944453Q

Visual Indicators	Part Number	Setting (bar)
	FMUM3MVMS08	5

For spare element see page 130.

Electrical Indicators	Part Number	Setting (bar)	Switch Type	Additional
	FMUT1MVMS08	5	NO/NC	
	FMUF1MVMS08	5	NO	Electronic 4 LED, PNP
	FMUF2MVMS08	5	NO	Electronic 4 LED, NPN
	FMUF3MVMS08	5	NC	Electronic 4 LED, PNP
	FMUF4MVMS08	5	NC	Electronic 4 LED, NPN

# High Pressure Filter

### **Ordering Information**

•								
Box 1	Box 2	Box 3	Box 4	Box 5	Box 6	Box 7	Box 8	
EPF3	2	02QI	В	Р	М	G16	1	
Box 1		Bo	x 2					

Capacity		
Model	Code	
Size 1 (40 l/min)	EPF1	
Size 2 (replaces 18P)	EPF2	
Size 3 (replaces 28P)	EPF3	
Size 4 (replaces 38P)	EPF4	
Size 5	EPF5	

Filter Length		
	Code	
Length 1	1	
Length 2 (not for Size 1 and Size 5)	2	

### **Highlights Key** (Denotes part number availability)

123	Item is standard
123	Item is standard green option
123	Item is semi standard
123	Item is non standard

#### Box 4

Seal Material		
	Code	
Nitrile	В	
Fluorelastomer	V	

Box 3

Degree of filtration				
	Media code			
iprotect® Glassfibre element	02QI	05QI	10QI	20QI
iprotect® with reverse flow valve(*)	02QIR	05QIR	10QIR	20QIR
iprotect® High Strength element	02QIH	05QIH	10QIH	20QIH

(\*Note: Only in combination with 3.5 bar bypass)

Box 5		
Indicator		
	Code	
Visual Indicator	М3	
Electrical Indicator	T1	
Electronic 4 LED, PNP, NO	F1	
Electronic 4 LED, NPN, NO	F2	
Electronic 4 LED, PNP, NC	F3	
Electronic 4 LED, NPN, NC	F4	
Plugged with Steel plug	Р	
No indicator port	N	

Other versions like ATEX on request All electrical indicators are CE-certified

#### Box 6

Bypass Setting			
	Indicator Setting	Code	
3.5 bar	2.5 bar	К	
5.0 bar	3.5 bar	L	
7.0 bar	5.0 bar	м	
No bypass	5.0 bar	м	
No bypass	No indicator	Х	

Important notes: When no bypass is selected Parker strongly advices the use of high strength elements

Box 8

Options		
		Code
Standard		1
No bypass		2
Reverse flow valve	Safeguard valve only in combination with 3.5 bar bypass	RFV
ATEX certified*		EX

(Cetegory 2, non-electrical equipment)

Note 1: For non-bypass please select High strength element type QIH Note 2': For ATEX classified filters add EX atter the code. ATEX certified filters with electrical indicator are available on request. Visual indicators are classified as Category 2, non electrical equipment. Filter assemblies with EX code will be supplied with a dedicated name plate. Pls consult Parker Filtration for any questions related to the classification of our products.

#### 

	Filter Connection	
	Connection type & size	Code
Size 1	Thread G1/2	G08
	Thread SAE 8	S08
Size 2	Thread G1/2	G08
	Thread G¾	G12
	Thread SAE 12	S12
	Thread M27, ISO 6149	M27
	SAE flange 3/4 - 6000M	H12
	SAE flange 3/4 - 6000	F12
	Manifold	X12
Size 3	Thread G1	G16
	Thread SAE 16	S16
	Thread M33, ISO 6149	M33
	SAE flange 1 - 6000M	H16
	SAE flange 1 - 6000	F16
Size 4	Thread G1¼	G20
	Thread G11/2	G24
	Thread SAE20	S20
	Thread SAE24	S24
	Thread M42, ISO 6149	M42
	SAE flange 11/4 - 6000M	H20
	SAE flange 1¼ - 6000	F20
	Manifold	X20
Size 5	Thread G11/2	G24
	Thread SAE 24	S24
	SAE flange 11/2 - 6000M	H24
	Manifold	X20

# ᠈ᡔ᠋ᡣᡘ