

### R2PR - PREMIER



### R1C - TEKNO 1SC



### R2C - TEKNO 2SC



### EV6 - EVEREST 6000



### 4STP - BRIDGESTONE 4ST+




### CPT1 - TEKNOJET 1SC



### CPT2 - TEKNOJET 2SC



Letku	Holkki	Puristusmitta Ø (mm)	Koko	Letku merkintä	Holkki tehdaskoodi	Työpaine (bar)	Holkki mitat D x L (mm)	Ulkokuorinta (mm)
R2PR-04	PB-04	16,2	1/4"	PREMIER 1/4"	B1SC04	450	20x30	ei kuorita
R2PR-05	PB-05	17,8	5/16"	PREMIER 5/16"	B1SC05	425	22x30	ei kuorita
R2PR-06	PB-06	20,0	3/8"	PREMIER 3/8"	B1SC06	390	24x32	ei kuorita
R2PR-08	PB-08	23,8	1/2"	PREMIER 1/2"	B1SC08	350	28x34	ei kuorita
R2PR-10	PB-10	28,0	5/8"	PREMIER 5/8"	B1SC10	350	32x37	ei kuorita
R2PR-12	PB-12	30,3	3/4"	PREMIER 3/4"	B1SC12	300	35x42	ei kuorita
R2PR-16	PB-16	37,9	1"	PREMIER 1"	B1SC16	230	43x51	ei kuorita
R1C-04	PB-04	15,3	1/4"	TEKNO 1SC 1/4"	B1SC04	225	20x30	ei kuorita
R1C-06	PB-06	18,6	3/8"	TEKNO 1SC 3/8"	B1SC06	180	24x32	ei kuorita
R1C-08	PB-08	22,5	1/2"	TEKNO 1SC 1/2"	B1SC08	160	28x34	ei kuorita
R1C-12	PB-12	29,2	3/4"	TEKNO 1SC 3/4"	B1SC12	105	35x42	ei kuorita
R1C-16	PB-16	36,9	1"	TEKNO 1SC 1"	B1SC16	88	43x51	ei kuorita
R2C-04	PB-04	16,2	1/4"	TEKNO 2SC 1/4"	B1SC04	400	20x30	ei kuorita
R2C-06	PB-06	20,0	3/8"	TEKNO 2SC 3/8"	B1SC06	330	24x32	ei kuorita
R2C-08	PB-08	23,8	1/2"	TEKNO 2SC 1/2"	B1SC08	275	28x34	ei kuorita
R2C-10	PB-10	27,8	5/8"	TEKNO 2SC 5/8"	B1SC10	250	32x37	ei kuorita
R2C-12	PB-12	30,3	3/4"	TEKNO 2SC 3/4"	B1SC12	215	35x42	ei kuorita
R2C-16	PB-16	37,9	1"	TEKNO 2SC 1"	B1SC16	165	43x51	ei kuorita
R2C-20	PXV-20	48,7	1 1/4"	TEKNO 2SC 1 1/4"	B12T20N	125	59x59	ei kuorita
R2C-24	PXV-24	56,2	1 1/2"	TEKNO 2SC 1 1/2"	B12T24N	100	67x67	ei kuorita
EV6-12	B5K-12	37,0	3/4"	EVEREST 6000 3/4"	B5K12	350	43,5x44	ei kuorita
EV6-16	B5K-16	44,7	1"	EVEREST 6000 1"	B5K16	350	51x54,4	ei kuorita
EV6-12	MRV-12	34,5	3/4"	EVEREST 6000 3/4"	B9R-12	350	38x45,2	36
EV6-16	MRV-16	42,3	1"	EVEREST 6000 1"	B9R-16	350	45x56	48
EV6-12	MXT-12	34,7	3/4"	EVEREST 6000 3/4"	BSN312	420	42x51	ei kuorita, MX-sisäosin
EV6-16	MXT-16	42,2	1"	EVEREST 6000 1"	BSN312	420	50x57	ei kuorita, MX-sisäosin
4STP-08	B5K-08	28,2	1/2"	4ST+ DN12	B5K08	350	35,5x36	ei kuorita
4STP-12	B5K-12	37,0	3/4"	4ST+ DN19	B5K12	350	43,5x44	ei kuorita
4STP-16	B5K-16	44,7	1"	4ST+ DN25	B5K16	350	51x54,4	ei kuorita
4STP-08	MRV-08	26,0	1/2"	4ST+ DN12	B9R08	350	30x34	27
4STP-10	MRV-10	30,0	5/8"	4ST+ DN16	B9R10	350	34x40	31
4STP-12	MRV-12	33,7	3/4"	4ST+ DN19	B9R12	350	38x45,2	36
4STP-16	MRV-16	41,0	1"	4ST+ DN25	B9R16	350	46x56	48
4STP-20	MRV-20	52,0	1 1/4"	4ST+ DN32	B9R20	350	59x66	54
4STP-12	MXT-12	34,7	3/4"	4ST+ DN19	BSN312	420	42x51	ei kuorita, MX-sisäosin
4STP-16	MXT-16	42,2	1"	4ST+ DN25	BSN316	420	50x57	ei kuorita, MX-sisäosin
4STP-20	MX-20A	51,3	1 1/4"	4ST+ DN32	BSN420A	420	62x68	ei kuorita, MX-sisäosin
CPT1-06	PB-04	15,3	1/4"	TEKNOJET 1SC 1/4"	B1SC04	250	20x30	ei kuorita
CPT1-05	PB-05	16,8	5/16"	TEKNOJET 1SC 5/16"	B1SC05	250	22x30	ei kuorita
CPT1-06	PB-06	18,6	3/8"	TEKNOJET 1SC 3/8"	B1SC06	250	24x32	ei kuorita
CPT2-04	PB-04	16,2	1/4"	TEKNOJET 2SC 1/4"	B1SC04	400	20x30	ei kuorita
CPT2-05	PB-05	18,0	5/16"	TEKNOJET 2SC 5/16"	B1SC05	400	22x30	ei kuorita
CPT2-06	PB-06	20,0	3/8"	TEKNOJET 2SC 3/8"	B1SC06	400	24x32	ei kuorita



Puristusmitat ovat viitteellisiä. Suosittelemme tarkistamaan puristusmitan aina tuurnaamalla.